










# Ekahau RTLS Wi-Fi Tags and Sensors



Tags & Sensors	Dimensions and Weight	Part #s	Battery Information	Mounting	Cleaning
<b>Ekahau A4 (Asset Tag)</b> 	1.8 x 2.2 x 0.7 in.	A4	2 x CR2 lithium batteries	Mount with double-sided tape, Velcro, Mounting plate (optional), or Hang mount (optional)	All Ekahau tags may be cleaned with basic healthcare cleaners, such as Cavicide, which can be liberally sprayed on the tags.
	45 x 55 x 19 mm.		Battery life: up to five years		
	Weight: 1.7 oz. or 48 g.		Alerts when battery is low		
<b>Ekahau A4+ (Asset Tag)</b> 	1.8 x 2.2 x 0.7 in.	A4+	External Battery: 2.5 – 5.5V DC	Mount with double-sided tape, Velcro, Mounting plate (optional), or Hang mount (optional)	All Ekahau tags may be cleaned with basic healthcare cleaners, such as Cavicide, which can be liberally sprayed on the tags.
	45 x 55 x 19 mm.		Backup Battery: 1xCR2 lithium batteries		
	Weight: 1.7 oz. or 48 g.		Alerts when battery is low		
<b>Ekahau B4 (Badge Tag)</b> 	2.36 x 3.54 x 0.33 in.	B4	Rechargeable	3-point break-away lanyard or clipped to a belt or pocket	All Ekahau tags may be cleaned with basic healthcare cleaners, such as Cavicide, which can be liberally sprayed on the tags.
	60 x 90 x 8.5 mm.		Battery life up to 300 hours at 15 second interval in blink mode		
	Weight: 1.7 oz. or 48 g.		Desk or rack charger (10)		
<b>Ekahau W4 (Wristband Tag)</b> 	2 x 1.9 x 0.7 in.	W4	Rechargeable Lithium Polymer battery	Standard hospital wristband that attaches through slots	Fully waterproof enabling easy cleaning.
	51.5 x 50 x 17.5 mm.		Battery life: up to 500h at 15second interval in blink mode		
	Weight: 1.09 oz. or 31 g.		Charging: Individual chargers and a 9 unit rack charger		

# Ekahau RTLS Wi-Fi Tags and Sensors



<b>Ekahau LB2 (IR Location Beacon)</b> 	4.9 x 2.6 x 2.0 in.	LB2	2 x 1.5 volt standard alkaline C batteries	Variety of mounting options included. No cabling required.	Standard dusting, dry cloth.
	125 x 67 x 51 mm. Weight: 1.4 oz. (w/o batteries)		Battery Life: 3-7 years depending on transmission interval and LED settings		
<b>Ekahau TS1 (Temp Sensor)</b> 	4.6 x 2.9 x 1.0 in.	TS1	2 x 3.6 volt standard lithium AA batteries	Tag body remains outside the cold storage and the probe is inserted through a small hole sealed with cable gland or putty (not included). Wall cradle (accessory) or inside the monitored unit	Standard dusting, dry cloth
	118 x 73 x 25 mm.		Battery Life of up to 3 years		
	Weight: 5.3 oz. or 347 g.				
<b>Ekahau TS2 (Temp Sensor)</b> 	4.6 x 2.9 x 1.0 in.	TS2	2 x 3.6 volt standard lithium AA batteries	Tag body remains outside the cold storage and the probe is inserted through a small hole sealed with cable gland or putty (not included)	Standard dusting, dry cloth
	118 x 73 x 25 mm.		Battery Life of up to 3 years		
	Weight: 5.3 oz. or 347 g.				
<b>Ekahau TSc (Temp Cube)</b> 	2.56 x 1.97 x 1.38 in.	TSc	2 X 1.5V Lithium AA battery	The tag sits completely in the cold storage. Tag can be affixed using a wall cradle (accessory)	Standard dusting, dry cloth
	65 x 50 x 35 mm.		Battery life up to 3 years		
	Weight: 4.0 oz. or 113 g.				
<b>Ekahau HS1 (Humidity Sensor)</b> 	4.5 x 2.75 x 1.0 in.	HS1	2 x 1.5 Volt standard lithium AA battery	Mounted on wall using a wall cradle (accessory) or inside the monitored unit	Standard dusting, dry cloth.
	114 x 70 x 25 mm.		Battery Life: Up to 3 years		
	Weight: 5 oz. or 142 g.				